

EPO-TEK® 301-2FL

Technical Data Sheet For Reference Only Low Stress, Optical Epoxy

Date: August 2021

Rev: ΧI No. of Components: Two Mix Ratio by Weight: 100:35 Specific Gravity:

Part A: 1.15

Pot Life: 10 Hours

Shelf Life- Bulk: One year at room temperature

Shelf Life-Syringe: Six months at -40°C Recommended Cure: 80°C / 3 Hours

Minimum Alternative Cure(s):

May not achieve performance properties listed below

23°C / 3 Davs

NOTES:

• Container(s) should be kept closed when not in use.

• Filled systems should be stirred thoroughly before mixing and prior to use.

- Performance properties (rheology, conductivity, others) of the product may vary from those stated on the data sheet when bi-pak/syringe packaging or post-processing of any kind is performed. Epoxy's warranties shall not apply to any products that have been reprocessed or repackaged from Epoxy's delivered status/container into any other containers of any kind, including but not limited to syringes, bi-paks, cartridges, pouches, tubes, capsules, films or other packages.
- If product crystalizes in storage, place container in warm oven until crystallization disappears. Please refer to Tech Tip #7 on website.

Part B: 0.95

Product Description: EPO-TEK® 301-2FL is a two component optical and semiconductor grade epoxy resin. It is a more flexible version of EPO-TEK® 301-2.

Typical Properties: Cure condition: 80°C / 3 Hours Different batches, conditions & applications yield differing results. Data below is not guaranteed. To be used as a guide only, not as a specification. * denotes test on lot acceptance basis

· ·		
PHYSICAL PROPERTIES:		
* Color (before cure):	Part A: Clear/Color	ess Part B: Clear/Colorless
* Consistency:	Pourable liquid	
* Viscosity (23°C) @ 100 rpm:	100 - 200	cPs
Thixotropic Index:	N/A	
* Glass Transition Temp:	≥ 45	°C (Dynamic Cure: 20-200°C/ISO 25 Min; Ramp -10-200°C @20°C/Min)
Coefficient of Thermal Expansion (CTE):		
Below Tg:	56	x 10 ⁻⁶ in/in°C
Above Tg	211	x 10 ⁻⁶ in/in°C
Shore D Hardness:	70	
Lap Shear @ 23°C:	> 2,000	·
Die Shear @ 23°C:	≥ 10	O , 1
Degradation Temp:	325	°C
Weight Loss:		
@ 200°C		
@ 250°C		%
@ 300°C		%
Suggested Operating Temperature:	< 250	°C (Intermittent)
Storage Modulus:	318,685	psi
Ion Content:	Cl ⁻ : 105 ppm	" "
	NH_4^+ : 8 ppm	K ⁺ : 19 ppm
Particle Size:	N/A	

ELECTRICAL AND THERMAL PROPERTIES:				
Thermal Conductivity:	N/A			
Volume Resistivity @ 23°C:	$\geq 0.6 \times 10^{12}$	Ohm-cm		
Dielectric Constant (1KHz):	3.54			
Dissipation Factor (1KHz):	0.013			

OPTICAL PROPERTIES @ 23	3°C:	
Spectral Transmission:	≥ 97% @ 1,000-1,600	nm
	≥ 99% @ 400-1,000	nm
Refractive Index:	1.5102 @ 589	nm

Epoxies and Adhesives for Demanding Applications™

This information is based on data and tests believed to be accurate. Epoxy Technology, Inc. makes no warranties (expressed or implied) as to its accuracy and assumes no liability in connection with any use of this product.

EPOXY TECHNOLOGY, INC.

14 FORTUNE DRIVE, BILLERICA, MA 01821 (978) 667-3805, FAX (978) 663-9782

www.epotek.com



EPO-TEK® 301-2FL

For Reference Only
Low Stress. Optical Epoxy

EPO-TEK®301-2FL Advantages & Suggested Application Notes:

- Suggested for LCD optical lamination and sealing of glass plates. The product can resist yellowing over 17 days of continuous UV light exposure. Suitable for LED encapsulation.
- Ease of use: potting and casting, encapsulation, and adhesive.
- Semiconductor applications: underfill for flip chips, glob top encapsulation over wire bonds, spin coating at wafer level.
- Compliant adhesive that will be resistant to impact or vibrations. Low stress adhesive for bonding optics inside OEM / scientific instruments.
- Fiber optic adhesive; bundling fibers, terminating fiber into ferrule, adhesive for mounting optics inside fiber components, bonding glass cover slip over V-groove; spectral transmission of visible and IR light.
- Adhesion to glass, quartz, metals, wood and most plastics is very good.
- May also be used for impregnating wooden or porous objects for artifact restoration.
- Capable of both heat cure and room temperature cure.